

Upright freezer XLT U250



- Optimal footprint
- Low cost of ownership
- Limited maintenance and on-site service
- Easily installable and movable

- Efficient cyclopentane insulation
- Eco-friendly, HCFC-free Nature R refrigerant
- Low energy consumption
- ISO 9001, 14001 & 18001 OHSAS Certified

Specifications

Technical

Gross volume	253 litres
Net Volume	221 litres
Temp. range	-30°C to -65°C
Temp. probes	1/PT 1000
Compressor	Secop
Refrigerant	Nature R
Noise level	60 dB
Power consumption 24/h	6,2 kWh
Power consumption	2.274 kWh / year
Voltage	230V
Frequency	50 Hz

Features

Audible and visual alarm	YES
Castors with brakes	4
Inner doors	2
Integrated lock	YES
Defrost	Manual
Battery Backup	48h
USB	YES
Data connection	MODBUS
Digital controller with display	XW737K
Data logging	35.000 Entries
High/Low temperature alarm	YES
Adjustable shelves, stainless steel	5
Door vacuum release	Automatic
Porthole for external probe & CO2 backup	Ø12 mm
Prepared for external logging equipment	YES
Contact for remote alarm	YES

Material

Inner	Stainless steel
Outer	Galvanized pre-coated steel

Dimensions

Height (with castors)	2.055 mm
Width	600 mm
Depth (incl. condenser)	630 mm
Depth (incl. condenser & handle)	690 mm
Net weight	120 kg

Internal dimensions

Height	1.420 mm
Width	420 mm
Depth	370 mm
Insulation	80 mm
Insulation type	PUR
Internal humidity	<5 %

XLT U250



Product no.

N122002

Opbevaringskapacitet

Boks højde	Antal bokse	Antal racks	Total antal bokse	Produkt nr.
50 mm	4 x 2 = 8	3	24	N321200
	5 x 2 = 10	12	120	N321210
			= 144	
75 mm	2 x 2 = 4	3	12	N321300
	3 x 2 = 6	12	72	N321310
			= 84	
100 mm	2 x 2 = 4	15	60	N321400